



Presets & Options:

- Mixer tap additionally available
- Vertical or horizontal drain
- Sleeve ground-shortly or wall-shortly
- Cold water, warm water, drain and electrical supply 230V or 400V must be presetted according to the regional directives
- Microsection direction:
Cupboards: side-walls, back-walls and doors vertical;
Ground, cap, socket, shelves and light-bar horizontal;
Work-plate: horizontal in position of installation;
NAB: vertical front, horizontal socket
Faceplate: vertical front ;
horizontal socket
- ATTENTION:** Please, take note of the fire detector!

		Discher Technik GmbH Fuhr 4-6, 42781 Haan-Gruiten Tel.: +49 (0)2104/2336-0 Fax: +49 (0)2104/233699 E-mail: info@discher.de	Type of machine: Master 1350 DT-L	
Customer-No.:			Surface: Microsection - polished with 240 grain size - finished with 280 grain size	
Project-No.:	Status:	 DISCHER		
Room:				
Date: 20.08.2015	Drawn by.: Schubert	Material: 1.4301	Scale: 1:20	
File name:		Measurements in mm		
<small>Duplication, even in extracts, requires the written permission of the Discher Company GmbH. State of the art and subject to change without prior notice.</small>				