



Presets & Options:

- Vertical or horizontal drain
- Sleeve ground-shortly or wall-shortly
- Cold water, warm water, drain and electrical supply 230V or 400V must be presetted according to the regional directives
- Microsection direction:
 Cupboards: side-walls, back-walls and doors vertical;
 Ground, cap, socket, shelves and light-bar horizontal;
 Work-plate: horizontal in position of installation;
 NAB: vertical front, horizontal socket
 Faceplate: vertical front ;
 horizontal socket
- **ATTENTION:** Please, take note of the fire detector!

		Discher Technik GmbH Fuhr 4-6, 42781 Haan-Gruiten Tel.: +49 (0)2104/2336-0 Fax: +49 (0)2104/233699 E-mail: info@discher.de	Type of machine: Master 1350.1 DT-R	
Customer-No.:			Surface: Microsection - polished with 240 grain size - finished with 280 grain size	
Project-No.:	Status:			Material: 1.4301
Room:				Scale: 1:20
Date: 14.08.2015	Drawn by.: Schubert			Measurements in mm
File name:		 DISCHER <small>Duplication, even in extracts, requires the written permission of the Discher Company GmbH. State of the art and subject to change without prior notice.</small>		